


SCF39XV-320-2R0B006JH

Aliases (UALCF390006JH0) Common Mode Chokes - Power, KEMET, SC39XV, Through-Hole, Common Mode, 900 uH, -30/+50%



Click here for the 3D mode	Click	here	for	the	3D	mode
----------------------------	-------	------	-----	-----	----	------

Comment of the second of the s	
General Information	
Series	SC39XV
Style	Through-Hole
Features	High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Nanocrystal

Dimensions	
D	53mm MAX
Н	31mm +1/-0.6mm
LL	4.5mm +/-0.5mm
S	24.84mm +/-0.1mm
S1	37.52mm +/-0.1mm
Wire Size	2.0 x 2 Parallel
BD	51mm +/-0.5mm
ВТ	50mm +/-0.5mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	48
Typical Component Weight	117.9 g

Specifications	
Voltage AC	1000 VAC
Voltage DC	1000 VDC
Inductance	0.9 mH
Inductance Tolerance	-30/+50%
Rated Current	32 A
Temperature Range	-40/+150°C
DC Resistance	1.13 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/27/2025 © 2006 - 2025 YAGEO