


## SCF39XV-400-Y2R0B003JH

Aliases (UALCF39Y003JH0) Common Mode Chokes - Power, KEMET, SC39XV-Y, Through-Hole, Common Mode, 230 uH, -30/+50%



General Information	
Series	SC39XV-Y
Style	Through-Hole
Features	High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Nanocrystal

Click here for the 3D model.

53mm MAX
31mm +1/-0.6mm
4.5mm +/-0.5mm
2.0 x 2 Parallel
51mm +/-0.5mm
50mm +/-0.5mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	48
Typical Component Weight	133.4 g

Specifications	
Voltage AC	1000 VAC
Voltage DC	1000 VDC
Inductance	0.23 mH
Inductance Tolerance	-30/+50%
Rated Current	40 A
Temperature Range	-40/+150°C
DC Resistance	0.53 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/13/2025 © 2006 - 2025 YAGEO