



Click [here](#) for the 3D model.

Dimensions

D	63mm MAX
T	39mm MAX
H	61mm MAX
LL	4.5mm +/-1.5mm
S	25mm NOM
S1	28mm NOM
Wire Size	1.8mm x 3P

Packaging Specifications

Packaging	Tray
Packaging Quantity	36
Typical Component Weight	190 g

General Information

Series	SCF-J/JH
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 75 K.
Core	Nanocrystal

Specifications

Voltage AC	500 VAC
Inductance	4 mH (10 kHz)
Current	40 A
Temperature Range	-40/+120°C
DC Resistance	2.1 mOhms