



Click [here](#) for the 3D model.

#### Dimensions

D	70mm MAX
H	36.5mm MAX
LL	6mm +/-3mm
S	44mm NOM
S1	32mm NOM
Wire Size	2.2mm x 3 Parallel

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	36
Typical Component Weight	135 g

#### General Information

Series	SCF-J/JH
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 35 K.
Core	Nanocrystal

#### Specifications

Voltage AC	500 VAC
Inductance	0.05 mH (100 kHz)
Current	60 A
Temperature Range	-40/+120°C
DC Resistance	0.31 mOhms