



Click [here](#) for the 3D model.

#### Dimensions

D	70mm MAX
H	38mm MAX
LL	5.1mm +/-1.5mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	27
Typical Component Weight	239 g

#### General Information

Series	SCF-X 3PHASE
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 60K.
Core	Nanocrystal

#### Specifications

Voltage AC	500 VAC
Voltage DC	500 VDC
Inductance	2.15 mH (100 kHz)
Current	30 A
Temperature Range	-40/+130°C
DC Resistance	2.31 mOhms