


## SCF47X-400-S2R2B007JH

Aliases (UALSCF47XS007H)

Common Mode Chokes - Power, KEMET, SC47X 3PHASE, Through-Hole, Common Mode, 1,300 uH



General Information	
Series	SC47X 3PHASE
Style	Through-Hole
Features	High Inductance, High Permeability
RoHS	Yes
Miscellaneous	Temperature Rise (K) Reference: 70.
Core	Nanocrystal

## Click here for the 3D model.

Dimensions		
D	70mm MAX	
Н	38mm MAX	
LL	4.5mm +/-1.5mm	
Packaging Specifications		
r dekaging opecinications		
Packaging	Tray	
Packaging Quantity	27	

234 g

Typical Component Weight

250 VAC
320 VDC
1.3 mH
40 A
-40/+130°C
1.53 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/24/2025 © 2006 - 2025 YAGEO