



Click [here](#) for the 3D model.

Dimensions

D	80mm MAX
H	45mm MAX
LL	5.1mm +/-1.5mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	18
Typical Component Weight	338 g

General Information

Series	SCF-X 3PHASE
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 65K.
Core	Nanocrystal

Specifications

Voltage AC	500 VAC
Voltage DC	500 VDC
Inductance	0.34 mH (100 kHz)
Current	80 A
Temperature Range	-40/+130°C
DC Resistance	0.55 mOhms