


SCF56X-400-S2R4B009JH

Aliases (UALSCF56XS009H)

Common Mode Chokes - Power, KEMET, SC56X 3PHASE, Through-Hole, Common Mode, 1,720 uH



General Information	
Series	SC56X 3PHASE
Style	Through-Hole
Features	High Inductance, High Permeability
RoHS	Yes
Miscellaneous	Temperature Rise (K) Reference: 65.
Core	Nanocrystal

Click here for the 3D model.

Dimensions		
D	80mm MAX	
Н	45mm MAX	
LL	4.5mm +/-1.5mm	
Packaging Specifications		

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	18	
Typical Component Weight	407 g	

Specifications	
Voltage AC	250 VAC
Voltage DC	320 VDC
Inductance	1.72 mH
Rated Current	40 A
Temperature Range	-40/+130°C
DC Resistance	1.84 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/24/2025 © 2006 - 2025 YAGEO