



Click [here](#) for the 3D model.

Dimensions	
D	29mm MAX
T	23mm MAX
H	29mm MAX
LL	4mm +/-1mm
S	18mm NOM
S1	16mm NOM
Wire Size	1.1mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	240
Typical Component Weight	25 g

General Information	
Series	SCR
Style	Through-Hole
Features	High Impedance
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	2 mH
Current	8 A
Temperature Range	-40/+120°C
DC Resistance	15.9 mOhms