


## SCR25XV-100-1R3A016JV

Aliases (UALCR250016JVO) Common Mode Chokes - Power, KEMET, SC25XV, Through-Hole, Common Mode, 3,100 uH



General Information	
Series	SC25XV
Style	Through-Hole
Features	High Impedance, High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
D	35.5mm MAX
T	26mm MAX
Н	32.5mm +1/-0.6mm
LL	3.5mm +/-0.5mm
S	20.5mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	1.3mm
BD	28.2mm +/-0.5mm
BT	25.50mm +/-0.5mm

Specifications		
Voltage AC	1000 VAC	
Voltage DC	1000 VDC	
Inductance	3.1 mH	
Rated Current	10 A	
Temperature Range	-40/+120°C	
DC Resistance	10.91 mOhms	

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	140	
Typical Component Weight	47.6 g	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/05/2025 © 2006 - 2025 YAGEO