



Click [here](#) for the 3D model.

Dimensions

D	48mm MAX
T	42mm MAX
H	35mm MAX
LL	4mm +/-1mm
S	17mm NOM
S1	30mm NOM
Wire Size	1.9mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	80
Typical Component Weight	87 g

General Information

Series	SCR31
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	79 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Inductance	1700 uH
Current	20 A
Temperature Range	-40/+120°C
DC Resistance	6.3 mOhms