



Click [here](#) for the 3D model.

#### Dimensions

D	39mm MAX
T	38mm MAX
H	15.5mm MAX
LL	5mm +/-2mm
S	10mm NOM
S1	35mm NOM
Wire Size	1.3mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	125
Typical Component Weight	31.6 g

#### General Information

Series	SCR-H
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	1.2 mH
Current	12 A
Temperature Range	-40/+120°C
DC Resistance	9.6 mOhms