



Click [here](#) for the 3D model.

#### General Information

Series	SCR38
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 65 K.
Core	Mn-Zn Ferrite

#### Dimensions

D	53.5mm MAX
T	53.5mm MAX
H	31.5mm MAX
LL	7mm +/-3mm
S	22mm NOM
S1	40mm NOM
Wire Size	1.8mm x 2 Parallel

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	48
Typical Component Weight	120 g

#### Specifications

Voltage AC	250 VAC
Inductance	0.85 mH
Current	35 A
Temperature Range	-40/+120°C
DC Resistance	2.5 mOhms