


SCR39XV-100-1R5A028JH

Aliases (UALCR390028JH0) Common Mode Chokes - Power, KEMET, SC39XV, Through-Hole, Common Mode, 0.0103 H, 35%



Click here for the 3D mode	Click	here	for	the	3D	mode
----------------------------	-------	------	-----	-----	----	------

General Information				
Series	SC39XV			
Style	Through-Hole			
Features	High Impedance, High Rated Voltage			
RoHS	Yes			
Qualifications	AEC-Q200			
AEC-Q200	Yes			
Notes	Lead Spacing (S/S1) Are For Reference Only.			
Miscellaneous	Temperature Rise Maximum: 45 K.			
Core	Mn-Zn Ferrite			

Dimensions	
D	53mm MAX
Н	31mm +1/-0.6mm
LL	4.5mm +/-0.5mm
S	24.84mm +/-0.5mm
S1	37.52mm +/-0.5mm
Wire Size	1.5mm
BD	51mm +/-0.5mm
BT	50mm +/-0.5mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	48
Typical Component Weight	122.2 g

Specifications	
Voltage AC	1000 VAC
Voltage DC	1000 VDC
Inductance	10.3 mH
Inductance Tolerance	35%
Rated Current	10 A
Temperature Range	-40/+120°C
DC Resistance	17.91 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/06/2025 © 2006 - 2025 YAGEO