



Click [here](#) for the 3D model.

#### Dimensions

D	70mm MAX
H	48mm MAX
LL	5mm +/-1.5mm
S	56mm NOM
Wire Size	2mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	27
Typical Component Weight	300 g

#### General Information

Series	SCR Three Phase
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 60 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Voltage DC	250 VDC
Inductance	2.5 mH (10 kHz)
Current	20 A
Temperature Range	-25/+120°C
DC Resistance	7.8 mOhms