


SCR47B-300-S1R7B020JH

Aliases (UALIF1R7B020JH)

Common Mode Chokes - Power, KEMET, SCR Three Phase, Through-Hole, Common Mode, 2,000 uH



Click [here](#) for the 3D model.

General Information

Series	SCR Three Phase
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	87 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Voltage DC	500 VDC
Inductance	2 mH
Rated Current	30 A
Temperature Range	-25/+120°C
DC Resistance	4.8 mOhms

Dimensions

D	70mm MAX
H	50mm MAX
LL	5mm +/-2mm
S	56mm NOM
Wire Size	1.7mm x 2 Parallel

Packaging Specifications

Packaging	Tray
Packaging Quantity	27
Typical Component Weight	340 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.