



Click [here](#) for the 3D model.

Dimensions

D	70mm MAX
T	70mm MAX
H	38mm MAX
LL	4.5mm +/-1.5mm
S	44mm NOM
S1	32mm NOM
Wire Size	1.6mm x 3P

Packaging Specifications

Packaging	Tray
Packaging Quantity	36
Typical Component Weight	210 g

General Information

Series	SCR47
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 75 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Inductance	1.6 mH
Current	35 A
Temperature Range	-40/+120°C
DC Resistance	3.5 mOhms