



Click [here](#) for the 3D model.

### Dimensions

D	53mm MAX
T	35mm MAX
H	51mm MAX
LL	10mm +/-5mm
S	15mm NOM
S1	26mm NOM
Wire Size	2.3mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	75
Typical Component Weight	110 g

### General Information

Series	SCR38
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	250 VAC
Inductance	1mH
Current	20 A
Temperature Range	-40/+120°C
DC Resistance	3.5 mOhms