


## SCT39XV-290-Y2R4A004JH

**General Information** 

Series

Aliases (UALCT39Y004JH0) Common Mode Chokes - Power, KEMET, SC39XV-Y, Through-Hole, Common Mode, 119 uH, 30%



Style	Through-Hole
Features	High Impedance, High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

SC39XV-Y

Click here for the 3D model.

Dimensions	
D	53mm MAX
Н	31mm +1/-0.6mm
LL	4.5mm +/-0.5mm
Wire Size	2.4mm
BD	51mm +/-0.5mm
BT	50mm +/-0.5mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	48
Typical Component Weight	120.3 g

Specifications		
Voltage AC	1000 VAC	
Voltage DC	1000 VDC	
Inductance	0.119 mH	
Inductance Tolerance	30%	
Rated Current	29 A	
Temperature Range	-40/+150°C	
DC Resistance	1.1 mOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO