



Click [here](#) for the 3D model.

## General Information

Series	SC25XV
Style	Through-Hole
Features	High Impedance, High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

## Specifications

Voltage AC	1000 VAC
Voltage DC	1000 VDC
Inductance	0.072 mH
Rated Current	35 A
Temperature Range	-40/+150°C
DC Resistance	0.65 mOhms

## Dimensions

D	37.5mm MAX
T	26mm MAX
H	32.5mm +/-0.6mm
LL	3.5mm +/-0.5mm
S	20.5mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	2.4mm
BD	28.2mm +/-0.5mm
BT	25.50mm +/-0.5mm

## Packaging Specifications

Packaging	Tray
Packaging Quantity	140
Typical Component Weight	47.6 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.