



Click [here](#) for the 3D model.

**General Information**

Series	SH
Style	Through-Hole
RoHS	Yes
Miscellaneous	For 2 Lines.

**Dimensions**

L	9mm MAX
W	10mm MAX
H	10.5mm MAX
LL	3mm +/-0.7mm
S	6.5mm MAX
S1	2.5mm NOM
F	0.6mm NOM

**Packaging Specifications**

Packaging	Bulk, Box
Packaging Quantity	3000
Typical Component Weight	1.12 g

**Specifications**

Voltage DC	50 VDC
Inductance	30 uH
Temperature Range	-25/+60°C
DC Resistance	51 mOhms (per Line MAX)