


## SH-S132

Aliases (UDLSH00S132000)

Not for New Design

EOL: 11-30-2026 / Last time buy date: 05-29-2026

Common Mode Chokes - Signal, KEMET, SH, Through-Hole, Common Mode, 1,700 nH



Click [here](#) for the 3D model.

### General Information

|               |              |
|---------------|--------------|
| Series        | SH           |
| Style         | Through-Hole |
| RoHS          | Yes          |
| Miscellaneous | For 3 Lines. |

### Dimensions

|    |              |
|----|--------------|
| L  | 9mm MAX      |
| W  | 10mm MAX     |
| H  | 10.5mm MAX   |
| LL | 3mm +/-0.7mm |
| S  | 6.5mm MAX    |
| S1 | 2.5mm NOM    |
| F  | 0.6mm NOM    |

### Packaging Specifications

|                          |    |
|--------------------------|----|
| Typical Component Weight | 1g |
|--------------------------|----|

### Specifications

|                   |                         |
|-------------------|-------------------------|
| Voltage DC        | 50 VDC                  |
| Inductance        | 1.7 uH                  |
| Temperature Range | -25/+80°C               |
| DC Resistance     | 81 mOhms (per Line MAX) |