



#### General Information

Series	SN-JA
Style	Through-Hole
RoHS	Yes
Miscellaneous	24 (K) Temperature Rise Max.
Core	Fe

#### Specifications

Inductance	108 uH (0.1 MHz)
Current	8 A
Temperature Range	-40/+105°C
DC Resistance	0.027 Ohms

Click [here](#) for the 3D model.

#### Dimensions

L	35mm MAX
T	20mm MAX
H	39mm MAX
LL	5mm +/-1.5mm
S	15mm NOM
Wire Size	1.5mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	45 g