



## SN12-500J

Specifications Inductance

Aliases (UALSN12500J000)

Differential Mode Chokes - Power, KEMET, SN-J, Through-Hole, Normal Mode, 100 uH





Click here for the 3D model.

Dimensions	
D	28mm MAX
W	22mm NOM
Т	17mm MAX
Н	29mm MAX
LL	7mm +/-2mm
S	10mm NOM
Wire Size	1mm

Rated Current	5 A
Temperature Range	-40/+105°C
DC Resistance	0.045 Ohms

100 uH

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	300	
Typical Component Weight	20 g	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO