


**General Information**

Series	SN-JA
Style	Through-Hole
RoHS	Yes
Miscellaneous	24 (K) Temperature Rise Max.
Core	Fe

[Click here for the 3D model.](#)
**Dimensions**

L	35mm MAX
T	20mm MAX
H	39mm MAX
LL	5mm +/-1.5mm
S	15mm NOM
Wire Size	1.5mm

**Specifications**

Inductance	108 uH
Rated Current	8 A
Temperature Range	-40/+105°C
DC Resistance	0.027 Ohms

**Packaging Specifications**

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	45 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.