



General Information

Series	SS11V/H-CH
Style	Through-Hole
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

Specifications

Voltage AC	250 VAC
Inductance	6.2 mH
Current	1 A
Temperature Range	-25/+120°C
DC Resistance	0.44 Ohms

Dimensions

L	21mm +/-1mm
T	20.5mm +/-1mm
H	16mm +/-1mm
LL	3.5mm +/-1mm
S	18mm +/-0.5mm
SI	14mm +/-0.5mm

Packaging Specifications

Typical Component Weight	11.1 g
--------------------------	--------