


SS11H-R17036-CH

Aliases (UAL11HR17036CH)

Not for New Design

Common Mode Chokes – Power, KEMET, SS11V/H-CH, Through-Hole Bobbin, Common Mode, 3,600 uH



General Information

Series	SS11V/H-CH
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

Dimensions

L	21mm +/-1mm
T	20.5mm +/-1mm
H	16mm +/-1mm
LL	3.5mm +/-1mm
S	18mm +/-0.5mm
S1	14mm +/-0.5mm
F	0.8mm NOM

Packaging Specifications

Typical Component Weight	10.8 g
--------------------------	--------

Specifications

Voltage AC	250 VAC
Inductance	3.6 mH
Rated Current	1.7 A
Temperature Range	-25/+120°C
DC Resistance	0.19 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.