



SS17HB-R05140

Aliases (UAL17HBR051400)

Not for New Design

Common Mode Chokes - Power, KEMET, SS17HB, Through-Hole Bobbin, Common Mode, 0.014 H





General Information	
Series	SS17HB
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530 or equivalent.

20mm MAX
17.85mm MAX
13.8mm MAX
2.5mm +/-0.5mm
16mm +/-0.5mm
10mm +/-0.5mm
0.25mm
0.7mm +/-0.1mm

Specifications	
Voltage AC	250 VAC
Inductance	14 mH
Rated Current	500 mA
Temperature Range	-25/+120°C
DC Resistance	1.1 Ohms

Packaging Specifi	cations
-------------------	---------

Typical Component Weight 6.4 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/12/2025 © 2006 - 2025 YAGEO