


## SS28V-R25080-CH

Aliases (UAL28VR25080CH, SS28V/H-R25080-CH)

Not for New Design

KEMET, SS28V/H-CH, AC Line Filters, Common Mode, 8 mH



### General Information

Series	SS28V/H-CH
Style	Through-Hole
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

### Specifications

Voltage AC	250 VAC
Inductance	8 mH
Current	2.5 A
Temperature Range	-25/+120°C
DC Resistance	0.16 Ohms

### Dimensions

L	30mm MAX
T	22mm MAX
H	35.5mm MAX
LL	4mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm

### Packaging Specifications

Typical Component Weight	32.9 g
--------------------------	--------