


## SS20H-08100

Aliases (UAL20H08100000)

Not for New Design

KEMET, SS20H, AC Line Filters, Common Mode, 10 mH



### General Information

Series	SS20H
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Inductance Measurement Condition: 1kHz IV KC530.

### Specifications

Voltage AC	250 VAC
Inductance	10 mH
Current	800 mA
Temperature Range	-25/+120°C
DC Resistance	0.66 Ohms

### Dimensions

L	22mm MAX
T	22mm MAX
H	18.5mm MAX
LL	3.5mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm

### Packaging Specifications

Typical Component Weight	12 g
--------------------------	------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.