



General Information

Series	SS26V
Style	Through-Hole
RoHS	Yes
Notes	Replacement For SS28V Type And SS24V Type.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	117 mH
Current	500 mA
Temperature Range	-40/+120°C
DC Resistance	2.4 Ohms

Click [here](#) for the 3D model.

Dimensions

L	26mm +/-1mm
T	20.5mm +/-1mm
H	30.5mm +/-1mm
S	10mm +/-0.5mm
SI	10mm +/-0.5mm
Wire Size	0.32mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	350
Typical Component Weight	25.3 g