



Click [here](#) for the 3D model.

Dimensions	
L	26mm +/-1mm
T	20.5mm +/-1mm
H	30.5mm +/-1mm
S	10mm +/-0.5mm
SI	10mm +/-0.5mm
Wire Size	0.37mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	350
Typical Component Weight	25.2 g

General Information	
Series	SS26V
Style	Through-Hole
RoHS	Yes
Notes	Replacement For SS28V Type And SS24V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Specifications	
Voltage AC	250 VAC
Inductance	68 mH
Current	700 mA
Temperature Range	-40/+120°C
DC Resistance	1.4 Ohms