


## SSR10V-07330

Aliases (UALR10V0733000)

Common Mode Chokes - Power, KEMET, SSR10V/H, Through-Hole Bobbin, Common Mode, 0.033 H



SSR10V/H
Through-Hole Bobbin
Small Standard Common Mode, High Permeability, Compact Size, Low Profile, Light Weight, High Impedance, Strong Inductance
Yes
55 (K) Temperature Rise Max.
Mn-Zn Ferrite

250 VAC

33 mH

700 mA -40/+120°C

Click here for the 3D model.

Dimensions	
L	23.5mm MAX
T	13mm MAX
Н	21mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.28mm
F	0.7mm NOM

Tray

600

9 g

**Packaging Specifications** 

Typical Component Weight

**Packaging Quantity** 

Packaging

13mm +/-0.5mm	DC Resistance	0.9 Ohms
10mm +/-0.5mm		
0.28mm		
0.7mm NOM		

Specifications
Voltage AC

Inductance

**Rated Current** 

Temperature Range

Generated 11/20/2025 © 2006 - 2025 YAGEO

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.