


SSR10H-11140

Aliases (UALR10H1114000)

Common Mode Chokes - Power, KEMET, SSR10V/H, Through-Hole Bobbin, Common Mode, 0.014 H



Н
•
-Hole Bobbin
ndard Common Mode, meability, Compact Profile, Light Weight, edance, Strong ce
mperature Rise Max.
errite
1

Click here for the 3D model.

Dimensions	
L	22mm MAX
T	18mm MAX
Н	13.5mm MAX
LL	3.5mm +/-0.5mm
S	17mm +/-0.5mm
S1	12mm +/-0.5mm
Wire Size	0.35mm
F	0.7mm NOM

Packaging Specifications	
Packaging	Tray
Packaging Quantity	300
Typical Component Weight	9 g

Specifications	
Voltage AC	250 VAC
Inductance	14 mH
Rated Current	1.1 A
Temperature Range	-40/+120°C
DC Resistance	0.37 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/26/2025 © 2006 - 2025 YAGEO