



Click [here](#) for the 3D model.

General Information

Series	SSR21NV/NH
Features	Compact Size, Light Weight, High Performance, Low DCR, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	45 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions

L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.5mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	420
Typical Component Weight	14.5 g

Specifications

Voltage AC	250 VAC
Inductance	6.4 mH (10 kHz)
Current	2 A
Temperature Range	-40/+120°C
DC Resistance	0.09 Ohms