



Click [here](#) for the 3D model.

General Information

Series	SSR21NVS/NHS
Features	High Performance, High Frequency, Broad Bandwidth
RoHS	Yes
Miscellaneous	45 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	23.5 mH (10 kHz)
Current	800 mA
Temperature Range	-40/+120°C
DC Resistance	0.42 Ohms

Dimensions

L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.32mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	420
Typical Component Weight	13 g