



General Information

Series	SSR21NVS-M/NHS-M
Features	High Performance, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	60 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	89 mH (10 kHz)
Current	600 mA
Temperature Range	-40/+120°C
DC Resistance	1.35 Ohms

Click [here](#) for the 3D model.

Dimensions

L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.25mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	420
Typical Component Weight	14.5 g