



Click [here](#) for the 3D model.

General Information

| | |
|---------------|--|
| Series | SSR21NV/NH |
| Style | Through-Hole Bobbin |
| Features | Compact Size, Light Weight, High Performance, Low DCR, High Impedance, Strong Inductance |
| RoHS | Yes |
| Miscellaneous | 45 (K) Temperature Rise Max. |
| Core | Mn-Zn Ferrite |

Dimensions

| | |
|-----------|----------------|
| L | 22mm MAX |
| T | 16mm MAX |
| H | 27mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 13mm +/-0.5mm |
| S1 | 10mm +/-0.5mm |
| Wire Size | 0.2mm |
| F | 0.8mm NOM |

Packaging Specifications

| | |
|--------------------------|--------|
| Packaging | Tray |
| Packaging Quantity | 450 |
| Typical Component Weight | 14.5 g |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 181 mH |
| Rated Current | 300 mA |
| Temperature Range | -40/+120°C |
| DC Resistance | 2.85 Ohms |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.