



Click [here](#) for the 3D model.

General Information

| | |
|---------------|---|
| Series | SSR21NV-M/NH-M |
| Features | High Performance, High Impedance, Strong Inductance |
| RoHS | Yes |
| Miscellaneous | 65 (K) Temperature Rise Max. |
| Core | Mn-Zn Ferrite |

Specifications

| | |
|-------------------|-----------------|
| Voltage AC | 250 VAC |
| Inductance | 6.4 mH (10 kHz) |
| Current | 3 A |
| Temperature Range | -40/+120°C |
| DC Resistance | 0.08 Ohms |

Dimensions

| | |
|-----------|----------------|
| L | 22mm MAX |
| T | 16mm MAX |
| H | 27mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 13mm +/-0.5mm |
| S1 | 10mm +/-0.5mm |
| Wire Size | 0.55mm |

Packaging Specifications

| | |
|--------------------------|--------|
| Packaging | Tray |
| Packaging Quantity | 450 |
| Typical Component Weight | 14.5 g |