



Click [here](#) for the 3D model.

General Information

Series	SSRH24NVS/NHS
Style	Through-Hole Bobbin
Features	Compact Size, Light Weight, High Performance, Low Rdc
RoHS	Yes
Miscellaneous	65 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Dimensions

L	25.5mm MAX
T	25.5mm MAX
H	18mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM
S1	21mm NOM
Wire Size	0.4mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	22.5 g

Specifications

Voltage AC	250 VAC
Inductance	50 mH (10 kHz)
Current	1.2 A
Temperature Range	-40/+120°C
DC Resistance	0.43 Ohms