



Click [here](#) for the 3D model.

#### General Information

Series	SSRH24NVS/NHS
Features	Compact Size, Light Weight, High Performance, Low Rdc
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 65 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	50 mH (10 kHz)
Current	1.2 A
Temperature Range	-40/+120°C
DC Resistance	0.43 Ohms

#### Dimensions

L	25.5mm MAX
T	20mm MAX
H	31mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM
S1	10mm NOM
Wire Size	0.4mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Typical Component Weight	25 g