



Click [here](#) for the 3D model.

General Information

Series	SSRH7H-M
RoHS	Yes
Notes	M08 Lot No.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	16.9 mH (10 kHz)
Current	800 mA
Temperature Range	-40/+120°C
DC Resistance	0.56 Ohms (Per Line)

Dimensions

L	18mm MAX
T	14.5mm MAX
H	12mm MAX
LL	3.5mm +/-0.5mm
S	13mm NOM
SI	10mm NOM
Wire Size	0.7mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	600
Typical Component Weight	5.2 g