



Click [here](#) for the 3D model.

#### General Information

|               |                                 |
|---------------|---------------------------------|
| Series        | SSRH7HS-M                       |
| RoHS          | Yes                             |
| Notes         | M03 Lot No.                     |
| Miscellaneous | Temperature Rise Maximum: 50 K. |
| Core          | Mn-Zn Ferrite                   |

#### Specifications

|                   |                      |
|-------------------|----------------------|
| Voltage AC        | 250 VAC              |
| Inductance        | 92.5 mH (10 kHz)     |
| Current           | 300 mA               |
| Temperature Range | -40/+120°C           |
| DC Resistance     | 3.18 Ohms (Per Line) |

#### Dimensions

|           |                |
|-----------|----------------|
| L         | 18mm MAX       |
| T         | 14.5mm MAX     |
| H         | 12mm MAX       |
| LL        | 3.5mm +/-0.5mm |
| S         | 13mm NOM       |
| SI        | 10mm NOM       |
| Wire Size | 0.7mm          |

#### Packaging Specifications

|                          |      |
|--------------------------|------|
| Packaging                | Tray |
| Packaging Quantity       | 600  |
| Typical Component Weight | 5.1g |