



General Information

| | |
|---------------|---------------------------------|
| Series | SU-10VD |
| Style | Through-Hole |
| RoHS | Yes |
| Miscellaneous | Temperature Rise Maximum: 45 K. |
| Core | Ni-Zn Ferrite |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 50 uH |
| Current | 1 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 0.2 Ohms |

Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|---------------|
| L | 18mm MAX |
| T | 16mm MAX |
| H | 20mm MAX |
| LL | 4mm MIN |
| S | 13mm +/-0.5mm |
| S1 | 10mm +/-0.5mm |
| Wire Size | 0.32mm |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Tray |
| Packaging Quantity | 700 |
| Typical Component Weight | 5.5 g |