



Click [here](#) for the 3D model.

Dimensions

| | |
|----|-------------------|
| D | 4.7mm +/-0.25mm |
| L | 12.04mm +/-0.79mm |
| L2 | 15.49mm MAX |
| LL | 38.1mm +/-6.35mm |
| F | 0.51mm +/-0.05mm |
| G | 3.45mm +0.79mm |

Packaging Specifications

| | |
|--------------------|---------------------------------|
| Packaging | T&R, 305mm, Class I, B = 52.4mm |
| Packaging Quantity | 2500 |

General Information

| | |
|----------------|--|
| Series | T215 CSR13 |
| Dielectric | MnO2 Tantalum |
| Style | Axial Hermetic |
| Description | Axial, Solid Tantalum, Hermetically Sealed, High Temp Solder, Military, CSR13 Style |
| Features | High Temperature Solder, Low Leakage |
| RoHS | No |
| Prop 65 | ⚠ WARNING: Cancer and reproductive harm - http://www.p65warnings.ca.gov . |
| Termination | Lead (SnPb) |
| Lead | Wire Leads |
| Qualifications | MIL-PRF-39003, CSR13 Style |
| AEC-Q200 | No |
| Construction | Hermetic |

Notes
Dimensions Include Insulating Sleeve. Lead Length Shown Is For Parts Supplied With Bulk Packaging, When Supplied On T&R Or Ammo, Lead Length Is Determined By Taping Specification.

Specifications

| | |
|-------------------------|--|
| Capacitance | 1.2 uF |
| Capacitance Tolerance | 10% |
| Voltage DC | 100 VDC (85C), 67 VDC (125C), 130 VDC (85C Surge), 5 VDC (85C Reverse) |
| Temperature Range | -55/+125°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 3% |
| Failure Rate | C (0.01%/1000 Hrs) |
| ESR | 7 Ohms (100kHz) |
| Ripple Current | 120 mAmps (100kHz) |
| Leakage Current | 0.5 uA |
| Testing and Reliability | Standard Testing To MIL-PRF-39003 |