



Click [here](#) for the 3D model.

Dimensions

| | |
|----|------------------|
| D | 6mm |
| H | 9.9mm |
| S | 2.54mm +/-0.38mm |
| LL | 12.7mm +/-1.26mm |
| F | 0.5mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 50 |

General Information

| | |
|-------------|---|
| Series | T350 |
| Dielectric | MnO2 Tantalum |
| Style | Radial |
| Description | Radial, Solid Tantalum, Conformal, Dipped |
| Features | Low Leakage |
| RoHS | Yes |
| Termination | Tin |
| AEC-Q200 | No |
| Notes | Longest Lead Is Positive. |

Specifications

| | |
|-----------------------|--|
| Capacitance | 22 uF |
| Capacitance Tolerance | 10% |
| Voltage DC | 16 VDC (85C), 10 VDC (125C), 0.16 VDC (125C Reverse) |
| Temperature Range | -55/+125°C |
| Dissipation Factor | 6% |
| Leakage Current | 2.6 uA |