


T354K476M020AT7301

Aliases (T354K476M020ATTR)

Not for New Design

T354, Tantalum, MnO2 Tantalum, Commercial Grade, 47 uF, 20%, 20 VDC, Radial, Solid Tantalum, Conformal, Dipped, 6.35mm



Click [here](#) for the 3D model.

Dimensions

D	8.9mm
H	15.5mm
S	6.35mm +/-0.38mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging	T&R, 305mm
Packaging Quantity	500

General Information

Series	T354
Dielectric	MnO2 Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Conformal, Dipped
Features	Low Leakage
RoHS	Yes
Termination	Tin
AEC-Q200	No
Construction	Conformal
Notes	Longest Lead Is Positive.

Specifications

Capacitance	47 uF
Capacitance Tolerance	20%
Voltage DC	20 VDC (85C), 13 VDC (125C), 0.2 VDC (125C Reverse)
Temperature Range	-55/+125°C
Dissipation Factor	8%
Leakage Current	4.3 uA