




Click [here](#) for the 3D model.

## General Information

|                          |                                                                                                                              |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Series                   | T493 Space                                                                                                                   |
| Dielectric               | MnO <sub>2</sub> Tantalum                                                                                                    |
| Style                    | SMD Chip                                                                                                                     |
| Description              | SMD, MnO <sub>2</sub> , Molded, Aerospace                                                                                    |
| Features                 | Aerospace                                                                                                                    |
| RoHS                     | No                                                                                                                           |
| Prop 65                  | <b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a> |
| SCIP Number              | 1dd2e1b8-26dd-4d52-927c-6f9d519011aa                                                                                         |
| Termination              | Tin Lead (SnPb)                                                                                                              |
| AEC-Q200                 | No                                                                                                                           |
| Typical Component Weight | 654.04 mg                                                                                                                    |

## Dimensions

|   |                    |
|---|--------------------|
| L | 7.3mm +/-0.3mm     |
| W | 4.3mm +/-0.3mm     |
| H | 4mm +/-0.3mm       |
| T | 0.13mm REF         |
| S | 1.3mm +/-0.3mm     |
| F | 2.4mm +/-0.1mm     |
| A | 3.8mm MIN          |
| B | 0.5mm +/-0.15mm    |
| E | 3.5mm REF          |
| G | 3.5mm REF          |
| P | 1.7mm REF          |
| R | 1mm REF            |
| X | 0.1mm +/-0.1mm REF |

## Packaging Specifications

|                    |            |
|--------------------|------------|
| Packaging          | T&R, 178mm |
| Packaging Quantity | 500        |

## Specifications

|                         |                                                                                    |
|-------------------------|------------------------------------------------------------------------------------|
| Capacitance             | 100 uF                                                                             |
| Tolerance               | 10%                                                                                |
| Voltage DC              | 16 VDC (85C), 10.72 VDC (125C)                                                     |
| Temperature Range       | -55/+125°C                                                                         |
| Rated Temperature       | 85°C                                                                               |
| Dissipation Factor      | 8% 120Hz 25C                                                                       |
| Failure Rate            | C (0.01%/1000 Hrs)                                                                 |
| ESR                     | 0.1 Ohms (100kHz 25C)                                                              |
| Ripple Current          | 1285 mA (rms, 100kHz 25C)                                                          |
| Leakage Current         | 16 uA (5min 25°C)                                                                  |
| Testing and Reliability | 10 Cycles Surge Current Testing At +25C After Weibull; Additional Testing Option C |