


B45198L1156K106

Aliases (T495A156K006ZGA3K87280)

Obsolete

Tantalum, MnO2 Tantalum, 15 uF, 10%, 6.3 VDC, SMD, Molded, Automotive, 3.8 Ohms, 3216, 1.8mm



Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
S	0.8mm +/-0.3mm
F	1.2mm +/-0.1mm
K	1.3mm TYP

Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	9000

General Information

Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, Molded, Automotive
Features	Automotive
RoHS	Yes
Termination	Gold
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	AEC-Q200.

Specifications

Capacitance	15 uF
Capacitance Tolerance	10%
Voltage DC	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6%
Failure Rate	N/A
ESR	3.8 Ohms (100kHz)
Ripple Current	91.3 mAmps (25C), 82.2 mAmps (85C), 36.5 mAmps (125C)
Leakage Current	0.9 uA