


TEPSLB30J336M8R

Aliases (PSLB30J336M8R-T&R)

PS/L, Tantalum, Polymer Tantalum, Commercial Grade, 33 uF, 20%, 6.3 VDC, SMD, Molded, Polymer, Low ESR, 70 mOhms, 3528, 1.2 mm, 0.8 mm



Click [here](#) for the 3D model.

General Information

Series	PS/L
Dielectric	Polymer Tantalum
Style	SMD Chip
Description	SMD, Molded, Polymer, Low ESR
Features	Low Profile, Low ESR
RoHS	Yes
Termination	Tin
AEC-Q200	No

Dimensions

L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
H	1.1mm +/-0.1mm
S	0.8mm +/-0.2mm
F	2.2mm +/-0.1mm

Packaging Specifications

Packaging	T&R, 178mm
-----------	------------

Specifications

Capacitance	33 uF
Tolerance	20%
Voltage DC	6.3 VDC (105°C), 8.2 VDC (Surge)
Temperature Range	-55/+105°C
Rated Temperature	105°C
Dissipation Factor	8%
Failure Rate	N/A
ESR	70 mOhms (25C, 100kHz)
Ripple Current	1035 mAmps (25C, 100kHz)
Leakage Current	20.7 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.